

SOLDERPRO™ 50

Specifications	
W/Cap	153 mm (6.0 in)
Length: W/Soldering tip	140 mm (5.5 in)
W/blow torch tip	142 mm (5.6 in)
Weight (when gas-filled)	60 g
Approximate temperature soldering tip	210~400°C (410~750°F)
Torch	1300°C (2400°F)
Gas container capacity	7 ml
Operating capacity (one gas filling)	30 min. at mid setting

Packing		
Item	PRO-50	PRO-50K
Packing (Inner Box/Carton)	24 / 96	12 / 24
Packaging	Blister/ Card	Tool Case W/ Clam Shell
Master Carton (L x W x H cm)	38.2x33.3x47.6	54.2x30.9x56.4
CU.FT.	2.1'	3'
N.W. (kg)	8.5	9.7
G.W. (kg)	10	11.8



SOLDERPRO™ 50

30W-70W POWER RANGE

C o r d l e s s B u t a n e P r o d u c t s A t T h e L e a d i n g E d g e

Anytime, Anywhere Compact Micro Butane Soldering Iron

Applications:

- Electrical/Electronic Circuit Repair
- Light Plumbing
- Jewelry, Eyeglass Frame Repair
- Model Building
- Arts and Crafts
- Dental Wax Corrections
- Thawing Frozen Locks

Features:


Equivalent to a power range 30-70 Watt.
Cordless, simple, safe operation anywhere.
Ready to use 20 seconds after ignition.
Tank capacity for 30 minutes of operation.
No cords, can be used anywhere.
No electrical interference.
Comes with soldering tip and protective cap.
Perfect compact size for shirt or pants pocket.



30W-70W POWER RANGE

SOLDERPRO™ 50

Basic Tips



Patents Pending
Worldwide

Colors:



The World's most popular pocket sized butane powered soldering irons.
The Pro-50 is a multi-function heat tool specifically designed for the hobby/DIY enthusiast.
30W-70W equivalent electrical power.

