

 tiskaj

▼ Base Data	
Application Method	Thread required sleeves onto the closed prongs. Expand the prongs and slide the wire into the sleeve opening. Close the prongs and hold the sleeve onto the wire and slide the tool away from it. It is advisable to use a lubricant to help removal of tool from the wire due to the elastic tension inherent in these elastomeric markers.
Colour	Red (RD)
Product Family	Helsyn SLP
Product Group	Rubber Tubing, Silicone
Type	SLP20RD
▼ Product Dimensions	
Inside Ø	2 mm
Supplied Ø D	2 mm
Wall (WT)	0.5 mm
▼ Logistic and Packaging	
EAN code	5022660065897
Quantity per	Per metre
▼ Material and Specifications	
Flammability	UL94 HB
Material	Silicone (SI)
Material Shortcut	SI
Operating Temperature	-65 °C to +180 °C, intermittent 250 °C
Specification	BS-2848 Type 5 Class 180T, BS-3858 Type 5, BS-3G-198 Type 4