





General ordering data

Order No.	9508770000
Part designation	NexT 38/26/20 4gp ss
Version	Ex enclosure, 205 mm, 380 mm, 260 mm, Stainless steel 1.4404
EAN	4008190499785
Qty.	1 pc(s).

Dimensions

Fixing dimension, height	250 mm
Fixing dimension, width	316 mm
Height	205 mm
Length	380 mm
Width	260 mm

General details

Cover fixing	Removable cover + M6 screws
Enclosure fixing	Outside mounting with 10 mm holes
Integral fixing	4 x 10 mm spacers
Sealing material	Chloroprene (cover & flange)
Version cover	closed
Colour	Miscellaneous
Surface finish	polished, chemically immersed
Class of protection to EN 60529	IP 66
Weight	7,500 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	85 °C

Screwed cable glands top/bottom

M 12	57
M 16	40
M 20	26
M 25	15
M 32	8
M 40	6

Screwed cable glands top/bottom


M 50	2
M 63	2
M 75	1
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	57
M16	40
M20	26
M25	15
M32	8
M40	6
M50	2
M63	2
M75	1
On housing side	left / right

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000049
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Similar products

Order No.	Part designation	Version
9523670000	NexT 38/26/20 0gp 7032	Ex enclosure, 205 mm, 380 mm, 260 mm, Sheet steel 1.5 mm (16 SWG)
9523530000	NexT 38/26/20 0gp ss	Ex enclosure, 205 mm, 380 mm, 260 mm, Stainless steel 1.4404
9522690000	NexT 38/26/20 1gp ss	Ex enclosure, 205 mm, 380 mm, 260 mm, Stainless steel 1.4404
9507890000	NexT 38/26/20 2gp 7032	Ex enclosure, 205 mm, 380 mm, 260 mm, Sheet steel 1.5 mm (16 SWG)
9508700000	NexT 38/26/20 2gp ss	Ex enclosure, 205 mm, 380 mm, 260 mm, Stainless steel 1.4404
9523110000	NexT 38/26/20 3gp 7032	Ex enclosure, 205 mm, 380 mm, 260 mm, Sheet steel 1.5 mm (16 SWG)
9522830000	NexT 38/26/20 3gp ss	Ex enclosure, 205 mm, 380 mm, 260 mm, Stainless steel 1.4404

9507960000	NexT 38/26/20 4gp 7032	Ex enclosure, 205 mm, 380 mm, 260 mm, Sheet steel 1.5 mm (16 SWG)
------------	------------------------	---