





PRODUCT NUMBER	NO. OF CONTACTS
10054365-18211LF	18 CONTACTS
10054365-20211LF	20 CONTACTS
10054365-24211LF	24 CONTACTS
10054365-28211LF	28 CONTACTS


寸法表 DIMENSIONS TABLE

NO. OF CONTACTS	A	B	C
18 CONTACTS	8.5	9.5	11.9
20 CONTACTS	9.5	10.5	12.9
24 CONTACTS	11.5	12.5	14.9
28 CONTACTS	13.5	14.5	16.9

n:極数
nNO. OF CONTACTS




導体接触面
CONDUCTIVE SIDE
FPC




RECOMMENDED PCB LAYOUT

推奨基板寸法



推奨FPC寸法
RECOMMENDED FPC




部品表 PARTS TABLE

部品番号 PART NO.	部品名 PART NAME	材 料 MATERIALS	数量 Q'TY	備 考 NOTE
①	ハウジング HOUSING	耐熱性ガラス繊維入りポリイミド樹脂 (UL94V-0) POLYAMIDE RESIN GLASS REINFORCE(UL94V-0)	1	色:白 COLOR:WHITE
②	アクチュエータ ACTUATOR	耐熱性ガラス繊維入りPPS樹脂 (UL94V-0) PPS RESIN GLASS REINFORCE(UL94V-0)	1	色:黒 COLOR:BLACK
③	コンタクト CONTACT	りん青銅 PHOSPHOR BRONZE	n	めっき:ニッケル下地金めっき PLATING:GOLD UNDER Ni PLATING
④	補強金具 FIXING TAB	りん青銅 PHOSPHOR BRONZE	2	めっき:ニッケル下地すずめっき PLATING:TIN UNDER Ni PLATING

注1. FPCは、熱硬化接着剤を使用し接着方式は、熱圧着とする。
Adhesive method of supporting tape shall be heat crimping method and thermosetting adhesive shall be used.
注2. コンタクト、補強金具の平坦度は、0.1以内。
Coplanarity for contact terminal and fixing tab must be within 0.1mm.

rev	ecn no	dr	date
A	J05-0359	HK	June 15,05
B	J06-0196	HK	May18,06
C	J07-0442	HK	Aug31,07
D	J08-0496	HK	Nov22,08
E	J09-0045	HK	Feb2,09
F	J12-0129	HK	Aug30,12

www.fciconnect.com			surface ☒	tolerance std	projection	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M.Koga	Aug.30'12	ANGULAR	LINEAR	size	Scale
Eng	M.Koga	Aug.30'12	5°	*	A2	DRAWING SCALE
Chr	K.Higuchi	Aug.30'12			ECN	J12-0129
Appr	M.Koga	Aug.30'12	Product family		Spec ref	Released
			58GF		10054365	Rev. F
			0.5mm PITCH FPC CONNECTOR (UPPER SIDE CONTACT)			
			catalog no		CUSTOMER	
					sheet 2 of 4	



PRODUCT NUMBER	NO. OF CONTACTS
10054365-30210EHLF	30 CONTACTS


NO.	部 品 名 PART NAME	PRODUCT NO.	材 質 MATERIAL	数 量 Q'TY	記 事 NOTE
1	リール REEL	-----	ポリスチレン POLYSTYRENE	1	色:白又は、黒 COLOR:WHITE or BLACK
2	プラスチック(エンボス)テープ PLASTIC (EMBOSS) TAPE	-----	PP又は、PET PP OR PET	1	
3	カバーテープ COVER TAPE	-----	ポリエステル POLYESTER	1	
4	コネクタ CONNECTOR	10054365-__21HLF	添付図面参照 SEE ATTACHD DWG.	4,000	

注記
1.本製品は、自動実装(SMT)対応、FPC用コネクタのプラスチックテープ梱包品である。
2.プラスチック(エンボス)テープ 及びリールの形状寸法は、JIS C 0806
(電子部品のテーピング(表面実装部品))に準ずる。

NOTES
1.THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC
AND COPS WITH AUTOMATIC MOUNTING (SMT)
2.SEE JIS 0806 (PACKING OF ELECTRONIC COMPONENTS ON
CONTINUOUS TAPES (SURFACE MOUNTING DEVICES))

rev	ecr no	dr	date
A	J05-0359	M.K	Mar.10,'05
B	J06-0196	M.K	May18,'06
C	J07-0442	M.K	Aug.31,'07
D	J08-0496	M.K	Nov.22,'08
E	J09-0045	M.K	Feb.2,'09
F	J12-0129	M.K	Aug.30,'12

www.fciconnect.com				surface	tolerance std	projection	mm
				✓	TOLERANCES UNLESS OTHERWISE SPECIFIED	size	
Dr	M.Kaga	Aug.20'12	ANGULAR	LINEAR	0.5	A2	Scale
Eng	M.Kaga	Aug.20'12	5°	*			DRAWING SCALE
Chr	K.Higuchi	Aug.20'12	Product family		58GF	ECN	J12-0129
Appr	M.Kaga	Aug.20'12				Spec ref	Released
FC				title			Rev.
				PLASTIC TAPE PACKAGED 0.5mm PITCH FPC CONNECTOR (UPPER SIDE CONTACT)			F
				dwg no			
				10054365			
				CUSTOMER			sheet 3 of 4



Copyright FCI