

ZBM 6/WH:UNBEDRUCKT

Order No.: 5061222

The illustration shows the versions ZBM and ZBFM in white

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=5061222>

Zack marker sheet, unprinted: 100-section, 10 strips à 10 markers, sufficient for 100 terminal blocks, with lettering area for application, for all terminal blocks, pitch 6.2 mm, labeling with M-PEN or CMS system, color: white

Commercial data

EAN	4017918096281
Pack	50 pcs.
Customs tariff	39269097
Weight/Piece	0.0177 KG
Catalog page information	Page 403 (CL-2005)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Color	white
Inflammability class acc. to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C
Components	free from silicone and halogen
Pitch	6.2 mm

Material	PA
Pitch	6.2 mm

Accessories

Item	Designation	Description
Marking		
1051993	B-STIFT	Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm
0811228	X-PEN 0,35	Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;