

### Product Description

Enables the use of cable glands with larger connection threads than the existing threaded holes; With guide notch for O-ring; Assembling with wrench



### Application range

- Equipment group II / Category 2G+1D
- Devices, machines and apparatus
- Mobile offshore and marine applications
- Chemical and petrochemical industry

### Benefits

- Enables the use of cable glands with larger connection threads than the existing threaded holes
- With guide notch for O-ring
- Assembling with wrench

### Design

- Metric connection thread acc. to EN 50262

## Technical Data

**Colour delivered**

RAL 7035 light grey

**Range of temperature**

-30°C up to +90°C

**Material**

Body: Nickel plated brass O-Ring: NBR

## Article List

| Part number          | Thread/<br>male M1 | Thread/<br>female M2 | Overall<br>height mm | SW<br>mm | Thread<br>length/<br>outside mm | Outer<br>Ø mm | PU |
|----------------------|--------------------|----------------------|----------------------|----------|---------------------------------|---------------|----|
| SKINDICHT® ME-M ATEX |                    |                      |                      |          |                                 |               |    |
| 52104580             | 12 x 1,5           | 16 x 1,5             | 17                   | 18       | 5                               | 20            | 50 |
| 52104581             | 16 x 1,5           | 20 x 1,5             | 20                   | 22       | 6                               | 24            | 50 |
| 52104582             | 20 x 1,5           | 25 x 1,5             | 22.5                 | 27       | 6.5                             | 30            | 50 |
| 52104583             | 25 x 1,5           | 32 x 1,5             | 21.5                 | 34       | 6.5                             | 37,7          | 25 |
| 52104584             | 32 x 1,5           | 40 x 1,5             | 23                   | 42       | 7                               | 46            | 25 |
| 52104585             | 40 x 1,5           | 50 x 1,5             | 26                   | 54       | 8                               | 59            | 25 |
| 52104586             | 50 x 1,5           | 63 x 1,5             | 32                   | 67       | 9                               | 73            | 10 |

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.