


4

3


2

1

LOC	DIST	REVISIONS				
FB	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			B1	REVISED PER ECO-11-005033	2APR11	RK HMR



TYPE 1







TYPE 2

VACUUM NOZZLE OUTLINE
(FOR REFERENCE)

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10>	: ±0.2
30> * >10	: ±0.25
100> * >30	: ±0.3
ANGLE	: ±3°

NOTE:
1. PEELING STRENGTH: 0.20-0.69N (20-70gf)
PEELING ANGLE: 165-180°
PEELING SPEED: 300mm/MINUTE.



		DWN S.XU 31JAN03	 TE Connectivity						
		CHK S.YAO 31JAN03							
		APVD T.SASAKI 31JAN03	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SINGLE ROW POST HDR ASS'Y (V)					
		0 PLC ± 1 PLC ± 2 PLC ± SEE L.H.S. 3 PLC ± 4 PLC ± ANGLES ±		SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED					
MATERIAL -		FINISH -		SIZE A3		CAGE CODE 00779	DRAWING NO C-292230	RESTRICTED TO -	
		WEIGHT -							
CUSTOMER DRAWING				SCALE NON		SHEET 1		OF 4	REV B1

THIS DRAWING IS UNPUBLISHED.
ALL RIGHTS RESERVED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY

LOC	DIST	REVISIONS							
FB	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
				SEE SHEET 1					

	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BLACK	7-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		6-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		6-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		6-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		6-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		6-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		6-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		6-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		6-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		6-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		6-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		5-292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		5-292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		5-292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		5-292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		5-292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		5-292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		5-292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
		TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL		POS
DIMENSIONS													

	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		1-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		1-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		1-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		1-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		1-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		1-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		1-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		1-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		1-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		1-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N	
	DIMENSIONS												

DIMENSIONS: mm		DWN	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	 TE Connectivity	
0 PLC ±-		APVD		
1 PLC ±0.1		PRODUCT SPEC	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH	
2 PLC ±0.01		SEE SHEET 1 OF 4	SINGLE ROW POST HDR ASS'Y (V)	
3 PLC ±0.001		APPLICATION SPEC	SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED	
4 PLC ±0.0001		SEE SHEET 1 OF 4	SIZE	RESTRICTED TO
ANGLES ±-		WEIGHT	CAGE CODE	
			DRAWING NO	
CUSTOMER DRAWING			A4 00779	G-292230
			SCALE	REV
			NON	B1
			SHEET 2 OF 4	

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	7-292230-0	2-292230-0
0.93	30.0	31.0	29.1	27.0	19	6-292230-9	1-292230-9
0.89	28.5	29.5	27.6	25.5	18	6-292230-8	1-292230-8
0.84	27.0	28.0	26.1	24.0	17	6-292230-7	1-292230-7
0.80	25.5	26.5	24.6	22.5	16	6-292230-6	1-292230-6
0.75	24.0	25.0	23.1	21.0	15	6-292230-5	1-292230-5
0.71	22.5	23.5	21.6	19.5	14	6-292230-4	1-292230-4
0.66	21.0	22.0	20.1	18.0	13	6-292230-3	1-292230-3
0.62	19.5	20.5	18.6	16.5	12	6-292230-2	1-292230-2
0.57	18.0	19.0	17.1	15.0	11	6-292230-1	1-292230-1
0.52	16.5	17.5	15.6	13.5	10	6-292230-0	1-292230-0
0.48	15.0	16.0	14.1	12.0	9	5-292230-9	292230-9
0.43	13.5	14.5	12.6	10.5	8	5-292230-8	292230-8
0.39	12.0	13.0	11.1	9.0	7	5-292230-7	292230-7
0.34	10.5	11.5	9.6	7.5	6	5-292230-6	292230-6
0.30	9.0	10.0	8.1	6.0	5	5-292230-5	292230-5
0.25	7.5	8.5	6.6	4.5	4	5-292230-4	292230-4
0.20	6.0	7.0	5.1	3.0	3	5-292230-3	292230-3
0.17	4.5	5.5	3.6	1.5	2	-	-
WEIGHT (g)	D	C	B	A	Pos.	BLACK	BEIGE (NAT)
	DIMENSIONS					P/N	

DIMENSIONS:		DWN	MATERIAL		FINISH	
mm		CHK	SEE SHEET 1		SEE SHEET 1	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	 TE Connectivity			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC				
		APPLICATION SPEC	NAME			
		WEIGHT	AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH			
			SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS			
			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A4	00779	C-292230	
CUSTOMER DRAWING			SCALE	NON	SHEET 4 OF 4	REV B1

