


DC Auto Power Plug

171-A13138-EX

KOBI CONN

DC Auto Power Plug

171-A13138-EX



Dimensions: mm (in.)

MATERIAL SPECIFICATIONS

Rating:	Input: 12/24 VDC
	Output: PSP 5 VDC 2000mA
	USB 5 VDC 450mA
Insulation Resistance:	DC 500V 100M Ω Min
Voltage Breakdown:	AC 1000V 1minute
Operating Temperature:	0°C~45°C
Fuse:	3A $\phi 5 \times 20$ Glass tube
Operation Force:	2.0~8.0kg
RoHS Compliant by Exemption	

Date Last Revised: 03/20/08

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301214

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-A13138-EX](#)