

Notes:

1. Material and Finish:

- Coupler Ring: Polyester (Black); UL94 V-0
- Plug Housing: Polyester (Black); UL94 V-0
- Cable Gland: PA (Black), UL94 V-0
- Cable Gland Rubber Ring: NBR, Color: Black
- Cable Fitting: PA (Black), UL94 V-0
- Interfacial Seal: Silicone, Color: White

(f) Duplex LC Connector

- Housing: PEI, UL94 V-0,

(e) (b) Color: **SM Blue/MM Beige/APC SM Green**





- Inner Sub Assembly: Zirconia, Metal and PTFE
- Crimp Barrel: Brass, Nickel Plated
- Ferrule: Brass, Nickel Plated
- Dust Cap: PC, Color: White

(c) Duplex LC Clip: PC, Color: Black

- Operating Temperature: -40°C to +85°C


2. IP67 rated when covered or fully mated with the appropriate mating connector

(d) 3. Accept 4.5mm to 8.0mm outside diameter fiber optic cable



Description	Part Number
Single Mode (SM)	17-300030
Multi Mode (MM)	17-300040
(e) APC Single Mode (APC SM)	17-300110

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	Customer:				Tolerance Unless otherwise specified				Scale: 1.5:1		Dim. in mm				
	Name		Title		Approval Date				Material: See Notes						
	g		1 x g		Sep/25/2013			Vincent Ke		2008		Date		Name	
	f		1 x f		Jul/12/2011			Vincent Ke		Draw.		Jun. 06		Vincent Ke	
	e		2 x e		Nov/22/2010			Vincent Ke		Appd.		Jun. 06		J. Chaudry	
	d		1 x d		Nov/03/2010			Vincent Ke		Norm.					
	c		1 x c		Jul/19/2010			Vincent Ke		D-old					
	b		1 x b		May/28/2009			Vincent Ke							
	a		original												
	Rev.		Changes		Date			Name							