

Y distributor - SAC-4PY-MT/2XFT VP - 1410632


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Y distributor, 4-position, Plug straight M12 SPEEDCON, T-coded, on Socket straight M12 SPEEDCON, T-coded and Socket straight M12 SPEEDCON, T-coded



Key Commercial Data

Packing unit	5 STK
GTIN	 4 046356 924726
GTIN	4046356924726

Technical data

Dimensions

Center distance	21 mm
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Degree of protection	IP65
	IP67

General

Rated current at 40 °C	2x 12 A (at 40 °C)
Rated voltage	63 V DC
Number of positions	4
Insulation resistance	≥ 100 MΩ
Coding	T power
Standards/regulations	IEC 61076-2-111
Status display	No
Overvoltage category	III
Degree of pollution	3
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 connector)

Y distributor - SAC-4PY-MT/2XFT VP - 1410632

Technical data

Material


Flammability rating according to UL 94	HB
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Standards and Regulations

Standards/regulations	IEC 61076-2-111
Flammability rating according to UL 94	HB


Drawings

Schematic diagram




Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Schematic diagram




Pin assignment of M12 socket, 4-pos., T-coded, socket side view

Dimensional drawing



M12 Y distributor

Circuit diagram



Contact assignment of the M12 Y distributor