




AMP WIRE RANGE	 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED

 LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1


STAMP AMP 8W* APPROX AS SHOWN
- 2

MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5MM ² [13,100-20,800] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

25	LOOSE PIECE, BOX	8-36906-3
----	LOOSE PIECE	36906
QUANTITY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-5-93	 TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK DA PATTERSON 4-5-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DE MILLER 4-5-93	NAME	
		PRODUCT SPEC	SPLICE, BUTT, SIGHT HOLE, SOLISTRAND™	
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	APPLICATION SPEC	RESTRICTED TO
WEIGHT ---		SIZE A2	CAGE CODE 00779	DRAWING NO G-36906
CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1	REV E1