



Shrink-Kon®

CMP250-0-A

Dual listed CSA / UR flexible heat shrink tubing.

T&B Catalog Number:	CMP250-0-A
EAN Number:	05414363102519
UPC Number:	78621082221
Description:	CMP thin wall dual listed UL/CSA heat shrink tubing, with expanded diameter 6.4 mm, black, shrink ratio 2:1, length 30.5 m (25 x 1.22m)



Technical Information

Tubing Family	CMP
Wall Thickness	thin
Shrink Ratio	2:1
Tube Characteristics	single wall
Material	PE crosslinked polyolefin
Temperature Range	-55°C to +125°C
Shrink Temperature	> +110°C
IP Rating	IP60
Flammability Rating	self-extinguishing
Colour	black
Silicone free	yes
Lead/Cadmium free	yes
Dielectric Strength	20 KV/mm
Chemical Resistance	very good

Approvals

UL recognised	E79546
CSA approved	702106

Ordering Information

Expanded Diameter as Supplied (inch)	1/4
Expanded Diameter as Supplied (mm)	6.4
Fully Recovered Diameter (mm)	3.2
Wall Thickness before Shrinking (mm)	0.3
Wall Thickness after Shrinking (mm)	0.6

Length (m)	30.5
Quantity per Box (pieces of 1.22 m)	25
Packaging Type	box