


Wall Mount - Smoked Glass Door Ventilated Rack Cabinets (SWCC Series)

Path: [Home](#) > [Rack Index](#) > Wall Mount - Smoked Glass Door - Ventilated Rack Cabinets (SWCC Series)



Click to enlarge

Features:

- Economic, light duty design - wall mount - 19" rack cabinet...
- Ventilated slots front & side...
- Body is hinged from wall mount section - 3.9" (100 mm) depth
- Pre-punched top for optional fans...
- Wall mount section includes cable access panels top & bottom...
- Both side panels are removable...
- Includes 2 - pair of mounting rails (square hole punched - with starter pack of push in nuts)...
- Includes smoked tempered glass door...
- Glass door opens a full 180 degrees for easy access to rack mount equipment...
- Glass door is easily removable and can be hinged either side...
- Glass door is complete with lock & key...
- Shipped assembled - ready to install.
- Recommended maximum static load weight - 130 pounds...
- Rugged black powder paint finish...

21.7" (550 mm) Deep Models - Includes 3.9" (100 mm) Wall Mount Section:



Part Number	Reader File		AutoCAD .dxf file (zipped)		Panel Height		Overall Height		Overall Width	
					Inches	Units	Inches	mm	Inches	mm
SWCC1901021BK2	NEW		NEW		10.50	6U	15.1	384	23.6	600
SWCC1901521BK2	NEW		NEW		15.75	9U	20.4	517	23.6	600
SWCC1902121BK2	NEW		NEW		21.00	12U	25.6	650	23.6	600
SWCC1902621BK2	NEW		NEW		26.25	15U	30.9	784	23.6	600
SWCC1903121BK2	NEW		NEW		31.50	18U	36.1	917	23.6	600

Note: We are working on drawings - available shortly.


SWCC - SERIES

Features


- Offered in 5 Heights all with overall width 600mm (23.6")
- Overall depth of 550mm (21.6") includes 100mm (3.9") deep wall mount sections and 450mm (17.7") deep hinged cabinet body
- Quick and easy wall mounting system
- Provides standard 19" rack mounting
- High quality, powder coat finish (black)
- Full-configured assembly includes:
 - Sturdy cold-rolled steel frame
 - Static load capacity of 60 kg (130lbs)
 - Ventilation slots front and side
 - Optional fans can be added into top cutouts
 - Hinged cabinets body can open 120 degrees
 - Body secured to wall mount section by lock and key
 - Wall mount section has cable access panels top and bottom
 - 2 pair of mounting rails
 - Square hole design, 20 screws and push-in nuts
 - 25mm incremental depth adjustment
 - Tempered glass door provides full view of equipment
 - Full 180 degree opening
 - Easily removed and can be hinged in either direction
 - Complete with lock and key
 - Pair of solid removable side panels



SECTION A-A



FRONT VIEW



SIDE VIEW

Part Number	Height (A)	Overall Width (B)	Overall Depth (C)
SWCC1901021BK2	384mm (15.1")6U	600mm (23.6")	550mm (21.7")
SWCC1901521BK2	517mm (20.3")9U	600mm (23.6")	550mm (21.7")
SWCC1902121BK2	650mm (25.6")12U	600mm (23.6")	550mm (21.7")
SWCC1902621BK2	784mm (30.8")15U	600mm (23.6")	550mm (21.7")
SWCC1903121BK2	917mm (36.1")18U	600mm (23.6")	550mm (21.7")