

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120380030

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for PROFIBUS, Classic 60mm, IP67, 8 Ports M12, 16 Inputs, NPN, 5 Pole Power

Documents:

Drawing (PDF)

Product Literature (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E200650

General

Product Family

Series

Application

Approvals

EPLAN

IP Rating

Overview

Product Literature Order No

Product Name

Protocol

Software Downloads

UPC

Industrial I/O Modules

112038

Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems

PI, UL, cUL, CE

Yes

IP67

IP67-Rated HarshIO Modules

987650-5701

HarshIO PROFIBUS DP

PROFIBUS DP

TCDPB-8xxx-xxx

78678890819

Physical

Bus Input

Bus Output

Format

Housing Width

I/O Connector

I/O Ports

I/O Signal Mix

Mechanical Shock

Net Weight

Power Input

Power Output

Temperature Range - Operating

Vibration

5-pole Micro-Change (M12), B-Coded, Male

5-pole Micro-Change (M12), B-Coded, Female

Classic (60mm)

60.00mm

5-pole Micro-Change (M12), A-Coded, Female

8x M12

16 input

10G, 11ms, 3 AXIS

560.000/g

5-pole Mini-Change, Male

5-pole Mini-Change, Female

-25°C to +70°C

IEC 60068-2-6

Electrical

Current - Maximum Output

EMC

Input Delay

Input Device Supply

Input Type

2.0A per Channel

IEC 61000-6-2

2.5ms

140 mA per port at 25°C

NPN or Dry Contact

Material Info

Engineering Number

TCDPB-8D0N-B1U

Reference - Drawing Numbers

Sales Drawing

1120380030-000, SD-112038-0024-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

112038 Series

This document was generated on 10/28/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION