

T12 Fluorescent Lamps

High Output 800, High Output

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
-----------------	----------------	--------------------	---------------	-------------	-------------	-------------------	-----------------------------	-----------------------------------	---------------------	-----

High Output 800 Series Fluorescent Lamps (800ma)

NEW!	95	14277-8		F96T12/830/HO/EW/ALTO	15	TL830, 3000K	86	12,000	8625	7750	85
		14278-6		F96T12/835/HO/EW/ALTO	15	TL835, 3500K	96	12,000	8625	7750	85
		14279-4		F96T12/841/HO/EW/ALTO	15	TL841, 4100K	96	12,000	8625	7750	85
		14280-4		F96T12/850/HO/EW/ALTO	15	TL850, 5000K	96	12,000	8520	7675	85

High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps (207, 214)

95	27319-3	X \$	F96T12/30U/HO/EW	15	Ultralume, 3000K	96	12,000	8625	7750	85
	34862-3	X \$	F96T12/41U/HO/EW	15	Ultralume, 4100K	96	12,000	8620	7750	85
	20525-2	X \$	F96T12/50U/HO/EW	15	Ultralume, 5000K	96	12,000	8520	7675	85
	34861-5	X \$	F96T12/SPEC30/HO/EW	15	SPEC30, 3000K	96	12,000	8350	7500	70
	22117-6	X \$	F96T12/SPEC35/HO/EW	15	SPEC35, 3500K	96	12,000	8350	7500	73
	34848-2	X \$	F96T12/SPEC41/HO/EW	15	SPEC41, 4100K	96	12,000	8350	7500	70
	21471-8	\$	F96T12/DX/HO/EW	15	Daylight Deluxe, 6500K	96	12,000	5850	5000	84
	26660-1	\$	F96T12/CW/HO/EW/ALTO	15	Cool White, 4100K	96	12,000	8000	6950	62
	34219-6	X \$	F96T12/WW/HO/EW	15	Warm White, 3000K	96	12,000	8100	7050	53
	34216-2	X \$	F96T12/LW/HO/EW	15	Lite White, 4200K	96	12,000	8300	7200	51

High Output 800 Series Fluorescent Lamps (800ma)

NEW!	110	14281-0		F96T12/830/HO/ALTO	15	TL830, 3000K	96	12,000	9500	8550	85
		14282-8		F96T12/835/HO/ALTO	15	TL835, 3500K	96	12,000	9500	8550	85
		14283-6		F96T12/841/HO/ALTO	15	TL841, 4100K	96	12,000	9500	8550	85
		14284-4		F96T12/850/HO/ALTO	15	TL850, 5000K	96	12,000	9350	8350	85

High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps (207, 214)

NEW!	110	34863-1	X	F96T12/30U/HO	15	Ultralume, 3000K	96	12,000	9500	8550	85
		26710-4	X	F96T12/35U/HO	15	Ultralume, 3500K	96	12,000	9500	8550	85
		34864-9	X	F96T12/41U/HO	15	Ultralume, 4100K	96	12,000	9500	8550	85
		34865-6	X	F96T12/50U/HO	15	Ultralume, 5000K	96	12,000	9350	8350	85
		27276-5	X	F96T12/SPEC30/HO	15	SPEC30, 3000K	96	12,000	9300	8375	70
		27681-6	X	F96T12/SPEC35/HO	15	SPEC35, 3500K	96	12,000	9300	8375	73
		27279-9	X	F96T12/SPEC41/HO	15	SPEC41, 4100K	96	12,000	9300	8375	70
		34226-1		F96T12/C50/HO	15	Colortone 50, 5000K	96	12,000	6300	5400	92
		34230-3	X	F96T12/N/HO	15	Natural, 3700K	96	12,000	6250	5400	90
		34222-0		F96T12/CWX/HO	15	Cool White Deluxe, 5000K	96	12,000	6600	5500	89
		21489-0		F96T12/DX/HO	15	Daylight Deluxe, 6500K	96	12,000	6750	5800	84

High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps; For Low Temperature Applications (223)

NEW!	110	38177-4		F96T12/D/HO-O/ALTO	15	Daylight, 6500K	96	12,000	7800	6800	79
		38176-4		F96T12/CW/HO-O/ALTO	15	Cool White, 4100K	96	12,000	8800	7650	62

For the most current product information, go to the e-catalog on www.philips.com

Fluorescent symbols and footnotes located on page 87

□ This product utilizes ALTO® Lamp Technology

X No longer manufactured, available until inventory depleted