

W2E143 Series

Tubeaxial

Ø 172x51mm



■ AC fans with external rotor shaded-pole motor.

■ Die-cast aluminum housing. Impeller of sheet-steel, directly welded onto rotor.

■ Air exhaust over struts. Rotational direction CCW looking at rotor.

■ Mounting from either face using two 4.6 mm holes.

■ Electrical connection via 2 flat pin terminals 2.8 x 0.5 mm.

■ Mounting from either face using 2 4.6 mm (.187") holes.

■ UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
W2E143-AA15-01	1	258.9	115	60*	26	60	70	Ball	Terminals	2.20
W2E143-AA09-01	1	258.9	230	60*	26	60	70	Ball	Terminals	2.20
W2E143-AB15-01	2	294.2	115	60*	29	58	75	Ball	Terminals	2.20
W2E143-AB09-01	2	294.2	230	60*	29	58	75	Ball	Terminals	2.20

* 50 Hz data available upon request

