

1595W

TradeMaster® Spec Grade 15 Amp Duplex GFCI, White - 1595W



TradeMaster/Spec Grade GFCI Receptacle with high-impact-resistant thermoplastic construction. It has SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. It prevents the line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Its mounting screws are shipped captive in the device and wall plate for easier installation. 10kA SCCR, 15A 125VAC, White

FEATURES

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal. Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Extra-long strap.
- Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

Specifications

DIMENSION INFO

Width U S: 1.72"

Depth U S: 0.98"

Height U S: 4.2"

1595W

LISTING AGENCY INFO

cULus

UL 39121614

BUY AMERICAN ACT COMPLIANCE

Country of Origin: CHINA

Buy American Act Status: No