

4-Wire eurofast® Cordsets, Standard Plug Body

- Straight Female Connector
- NEMA 1, 3, 4, 6P and IEC IP 68 Protection
- 250 VAC/300 VDC, 4 A



Housing Style	Part Number	Cable	Features	Pinout
RK ..** RKK ..** RKV ..**	RK 4.41T-*	AWM PVC NAMUR Blue 4x22 AWG 105°C 5.2 mm OD Cable #RF50598-*M†	flexlife®	1. BN 2. WH 3. BU 4. BK
	RK 4.41T-*/S529	AWM PUR/Heavy Braid Double Jacket Yellow 4x20 AWG 105°C 5.8 mm OD Cable #RF50526-*M†	Cut/Abrasion Immune Braided Mechanical Shield	
	RK 4.43T-*	AWM PVC Yellow 4x22 AWG 105°C 5.2 mm OD Cable #RF50530-*M†	flexlife	
	RK 4.43T-*/S90	AWM PUR Yellow 4x22 AWG 105°C 5.2 mm OD Cable #RF50613-*M†	Cut/Abrasion Immune	
	RK 4.4T-*	AWM PVC Grey 4x22 AWG 105°C 5.2 mm OD Cable #RF50516-*M†	flexlife	
	RK 4.4T-*/S90	AWM PUR Grey 4x22 AWG 105°C, 5.2 mm OD Cable #RF50532-*M†	Cut/Abrasion Immune	
	RK 4.4T-*/S101	AWM TPE Grey 4x22 AWG 105°C, 5.7 mm OD Cable #RF50941-*M†	flexLife-10, High Flex Over 10 Million Cycles	
	RK 4.4T-*/S824	PLTC PVC Grey 4x22 AWG 105°C, 5.2 mm OD Cable #RF50698-*M†	Tray Rated	
	RK 4.4T-*/S618	AWM PVC Grey 4x22 AWG Foil/Drain 105°C, 5.2 mm OD Cable #RF50577-*M†	RFI/EMI Shielding	
	RK 4.4T-*/S618/S824	PLTC PVC Grey 4x22 AWG Foil/Drain 105°C, 5.2 mm OD Cable #RF50773-*M†	RFI/EMI Shielding Tray Rated	

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKV .." indicates 316 stainless steel.

† See Section N for reelfast® cable information.