


**Models 72919**  
**2mm SAFETY Sheathed Patch Cords**



## Features

- 2mm Male to male straight fixed safety patch cord mates with 2mm jacks.

## Materials

- Wire Insulation: PVC
- Plug Body: Nickel plated Brass
- Plug Insulation: Polypropylene
- Plug Tip Insulation: Polysulfone

## Ordering Information

Model: 72919-Length-Color

Available lengths: 20 inches (-20) or 39 inches (-39)

Available colors: Black (-0) or red (-2)

## Specifications

|                |                  |
|----------------|------------------|
| Max Current    | 10A              |
| Max Voltage    | 33 Vrms / 70 Vdc |
| Temperature    | -20° C + 80° C   |
| Max Resistance | 0.02Ω            |

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 International: 425-446-5500

e-mail: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

Where to Buy: [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm 0.02''$  (.51 mm), .xxx =  $\pm 0.005''$  (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.