



THIS DOCUMENT CONTAINS DATA
 PROPRIETARY TO PROJECTS UNLIMITED, INC.
 ANY USE OR REPRODUCTION, IN ANY FORM,
 WITHOUT PRIOR WRITTEN PERMISSION OF
 PROJECTS UNLIMITED, INC. IS PROHIBITED.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RESONANT FREQUENCY	6,400±500	Hz
RESONANT IMPEDANCE (MAX)	500	Ohms
MAX INPUT VOLTAGE	30	Vp-p
CAPACITANCE @ 1KHz	14,000±30%	pF
PLATE MATERIAL	BRASS	—
OPERATING TEMP.	-20 ~ +60	°C
STORAGE TEMP.	-20 ~ +70	°C



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
 AB2064B.DWG

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	11/28/01	S. J.
A	REVISED TO NEW TEMPLATE	9/4/03	R. W.
B	REVISED DIMENSION SIZE AND STYLE	12/22/05	B. R.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN
 MILLIMETERS; TOLERANCES ARE ±0.5 AND
 ANGLES ARE ±3°.



Dayton , Ohio

PIEZO CERAMIC BENDER

APPROVALS
 DRAWN *RABL* 11/01

APPROVED *S. J.* 11/01

SIZE
 A

DRAWING NO.
 AB2064B

DO NOT SCALE DRAWING

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AB2064B](#)