





brass accessories

0123 barbed adapter for rubber hose — BSPT



ØD mm	C BSPT		ØD1 mm	F mm	L mm	L1 mm	T min mm	kg
4	R1/8	0123 04 10	6	10	34	22.5	3.3	.008
6	R1/8	0123 06 10	8	10	34	22.5	5	.009
7	R1/8	0123 07 10	9	10	34	22.5	5	.009
7	R1/4	0123 07 13	9	14	38.5	22.5	6	.018
7	R3/8	0123 07 17	9	17	39	22.5	6	.023
10	R1/8	0123 10 10	12.2	13	34	22.5	5	.014
10	R1/4	0123 10 13	12.2	14	38.5	22.5	7	.021
10	R3/8	0123 10 17	12.2	17	39	22.5	9.5	.023
12	R3/8	0123 12 17	14	17	46	29.5	11	.026
13	R1/4	0123 13 13	15	17	45.5	29.5	7	.027
13	R3/8	0123 13 17	15	17	46	29.5	11	.027
13	R1/2	0123 13 21	15	22	50.5	29.5	12	.047
16	R3/8	0123 16 17	18.5	19	54.5	38	11	.040
16	R1/2	0123 16 21	18.5	22	59	38	14	.056
16	R3/4	0123 16 27	18.5	27	62	38	15	.082
19	R3/8	0123 19 17	21.5	22	54.5	38	11	.046
19	R1/2	0123 19 21	21.5	22	59	38	14	.058
19	R3/4	0123 19 27	21.5	27	62	38	18	.083
25	R3/4	0123 25 27	26.7	27	62	38	18	.083
25	R1"	0123 25 34	27	36	65	38	24	.124
32	R1"	0123 32 34	34.5	36	70	43	24	.144

0136 barbed adapter for nylon tube — BSPT




ØD mm	C BSPT		ØD1 mm	F mm	L mm	L1 mm	T min mm	kg
4	R1/8	0136 06 10	4.3	10	26.5	15	2	.007
4	R1/4	0136 06 13	4.3	14	31	15	2	.015
4	R3/8	0136 06 17	4.3	17	31.5	15	2	.020
6	R1/8	0136 08 10	6.4	10	26.5	15	4	.007
6	R1/4	0136 08 13	6.4	14	31	15	4	.015
6	R3/8	0136 08 17	6.4	17	31.5	15	4	.020
8	R1/4	0136 10 13	8.4	14	31	15	6	.016
8	R3/8	0136 10 17	8.4	17	31.5	15	6	.020
8	R1/2	0136 10 21	8.4	22	36	15	6	.039
10	R1/4	0136 12 13	10.7	14	36	20	7	.019
10	R3/8	0136 12 17	10.7	17	36.5	20	8	.023
10	R1/2	0136 12 21	10.7	22	41	20	8	.040
12	R1/4	0136 14 13	12.7	14	36	20	7	.019
12	R3/8	0136 14 17	12.7	17	36.5	20	10	.023
12	R1/2	0136 14 21	12.7	22	41	20	10	.042
12	R3/4	0136 14 27	12.7	27	44	20	10	.072
13	R3/8	0136 16 17	13.7	17	36.5	20	11	.023
13	R1/2	0136 16 21	13.7	22	41	20	11	.041
13	R3/4	0136 16 27	13.7	27	44	20	11	.071

The 2 central digits in the product code part number represent the tube O.D. Ex: 0136 16 27

This range of adapters is limited to the maximum size (16 x 13) of Legris nylon tube.

0931 barbed adapter for rubber hose — BSPP



ØD mm	C BSPP		ØD1 mm	E mm	F mm	K mm	L mm	kg
6	G1/8	0931 06 10	7	6	12	4	20	0.008
6	G1/4	0931 06 13	7	8	14	5	20	0.013
7	G1/8	0931 07 10	8	6	12	4	20	0.009
7	G1/4	0931 07 13	8	8	14	5	20	0.017
7	G3/8	0931 07 17	8	9	19	5	20	0.022
8	G1/8	0931 08 10	9	6	12	4	20	0.009
8	G1/4	0931 08 13	9	8	14	5	20	0.014
8	G3/8	0931 08 17	9	9	19	5	20	0.022
10	G1/4	0931 10 13	12	8	14	5	20	0.016
10	G3/8	0931 10 17	12	9	19	5	20	0.023
10	G1/2	0931 10 21	12	10	22	6	22	0.032
15	G3/8	0931 15 17	17	9	19	6	24	0.030
15	G1/2	0931 15 21	17	10	22	6	24	0.036
18	G1/2	0931 18 21	20	10	22	6	24	0.043