



P DETAIL 6:1










示意图 SCHEMATIC



安装位置尺寸 LAND DIMENSION

规格 Specifications

额定负荷 Ratings	DC 5 V 1 mA
初期接触电阻 Initial Contact Resistance	5 Ω Max.
绝缘电阻 Insulation Resistance	DC 100 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 100 V(50~60HZ) 60 Sec.

操作力 Operating Force(gf)	60 Max.
负荷寿命 Operating Life With Load	50,000 次 Cycles

06	端子 TERMINAL	C5210R	4	Ag PLATED
05	弹簧 SPRING	SUS	1	NATURAL
04	弹片 SPRING PLATE	C5210R	1	NATURAL
03	盖片 COVER PLATE	SPT	1	NATURAL
02	胶柄 KNOB	PA (A)	1	BLACK C
01	胶壳 HOUSING	LCP	1	BLACK C
序NO.	零件PART	材料MATERIAL	数量QTY	备注REMARKS

A02	1、胶柄材料更改: LCP更改为PA, 见标示 (A); 2、修改胶柄工艺孔形状, 见标示 (A).	钟远禄	2009-3-26
A01		张渠江	2008-10-5
标号REV	内容DESCRIPTION	签名SIGN.	日期DATE

DWG NO. ITEM3040

TOLERANCES UNLESS OTHERWISE SPEC.	TITLE	DETECTOR SWITCH	ITEM NO	DS-180 RT
UNDER 1	± 0.10	DRAWN	钟远禄	2009-3-26
1 - 10	± 0.30	REVIEWED	方勇	2009-3-26
OVER 10	± 0.50	APPROVED	马建和	2009-3-26
			VERSION	A02
			SCALE	—
			PROJECTION	UNIT mm

COMAX

高铭电子(惠州)有限公司
Comax Electronics(Huizhou)Co.,Ltd.