


DATA SHEET N° DS/156	PLOTTER SYSTEM TAG HOLDER				DATE: 1/8/2007			
PICTURE								
								
REFERENCE ITEM CODE								
SIT0A06X - SIT0A07X - SIT0A08X - SIT0A06 -SIT0A06MC - SIT0A07 -SIT0A07MC - SIT0A08 - SIT0A08MC								
APPLICATION								
These items can be either adhesive (SIT0A06, SIT0A06MC, SIT0A07, SIT0A07MC, SIT0A08, SIT0A08MC) or non-adhesive (SIT0A06X, SIT0A07X, SIT0A08X) and allow marking push buttons carrying marker (tags for use with SI2000 plotter system) and protecting slide. Non adhesive items can be fixed by using screws, rivets or cable ties.								
PHYSICAL PROPERTIES								
MATERIAL				POLYAMIDE WITH GLASS FILLER				
FIRE RESISTANCE				CLASS V0 IN COMPLIANCE WITH UL - 94 NORMS				
ADHESIVE PHYSICAL PROPERTIES								
ADHESIVE MASS				MODIFIED ACRYLIC				
THICKNESS				0,4 mm				
TENSILE STRENGTH				22 N / 25 mm				
ELONGATION %				300				
APPLICATION TEMPERATURE				> 10 °C				
OPERATIVE TEMPERATURE				MAX 100 °C				
ITEM CODE		DIMENSIONS [mm]				COLOR	ADHESIVENESS	PIECES PER PACK
		A	B	C	D			
SIT0A06X		27.4	15.2	30	17.4	BLACK	NON-ADHESIVE	192 PCS
SIT0A07X		49.9	15.2	52.5	17.4	BLACK	NON-ADHESIVE	96 PCS
SIT0A08X		67.4	15.2	70	17.4	BLACK	NON-ADHESIVE	96 PCS
SIT0A06		27.4	15.2	30	17.4	BLACK	ADHESIVE	192 PCS
SIT0A06MC		27.4	15.2	30	17.4	BLACK	ADHESIVE	400 PCS
SIT0A07		49.9	15.2	52.5	17.4	BLACK	ADHESIVE	96 PCS
SIT0A07MC		49.9	15.2	52.5	17.4	BLACK	ADHESIVE	200 PCS
SIT0A08		67.4	15.2	70	17.4	BLACK	ADHESIVE	96 PCS
SIT0A08MC		67.4	15.2	70	17.4	BLACK	ADHESIVE	200 PCS
NOTES:								
Document Number	REVIEWED, APPR. BY:	DATE:		REVISION ISSUE			PAGES	
78-8127-9037-2		1/8/2007					1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[SIT0A06](#) [SIT0A06X](#) [SIT0A07](#) [SIT0A07X](#) [SIT0A08](#) [SIT0A08X](#)