



DIMENSIONS: mm (in)				
Part Number	A	B	C	Color
450-KB100	10 (.394)	8 (.315)	3.2 (1.26)	Natural
450-KB101	10 (.394)	8 (.315)	3.2(1.26)	Black
450-KB200	20 (.787)	15 (.591)	6.4(.525)	Natural
450-KB201	20 (.787)	15 (.591)	6.4(.525)	Black
450-KB300	30 (1.81)	25 (.984)	6.4(.525)	Natural
450-KB301	30 (1.81)	25 (.984)	6.4(.525)	Black

SPECIFICATIONS	
Material:	Aluminum
Finish:	Knurled
Tolerance:	±0.20
Hex Screw:	M3xP0.5xH3