


**Part Number: 68131-0230**

Automotive Filtered Horn Header, Rivet Diameter 100.00mm, 2 Circuits, White



Series Image - Reference only

Status: Planned for Obsolescence
Series: 68131
Category: PCB Headers

Mates With Part(s):
[35825](#)**Product Environmental Compliance**[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#): Contains SVHC: No[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

Status	Planned for Obsolescence
Category	PCB Headers
Series	68131
Application	Power, Wire-to-Board
Product Name	N/A

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Number of Rows	1
Orientation	Vertical
Pitch - Mating Interface	5.00mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Screw or Lug

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	10A
Voltage - Maximum	300V

Material Info

UPC	756054301784
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-68131-002
Sales Drawing	SD-68131-003

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application
Tooling**
[Check our list of old tooling that used to be
available for this part](#)