












1. 嵌合相手ハウジング型番
24P:1318756 26P:1318757
24P:1746864 26P:1746863
- △. 回路番号: FIG.1参照
3. 推奨取付ねじ: JIS B1115, B1122タリピンねじ 長さ: TABLE-1参照
4. ねじ締めトルク: 0.392N・m MAX(参考)
5. 本製品の取扱は、取扱説明書 No.411-5927に従うこと。
△. 3次DTMについては、[-S-], [-T-]を各々のブロック毎に適用すること。
△. [-Z-]より7.5mmの位置で測定。
△. コンタクト上識別用マーク
△. [-Z-]より2mmの位置で測定。
△. ID MARK, PART NUMBERを表示
1. PART NO. OF PLUG HOUSINGS TO BE MATED
24P:1318756 26P:1318757
24P:1746864 26P:1746863
- △. CIRCUIT NUMBER: SEE FIG.1
3. RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW,
NOMINAL DIAMETER 3mm
LENGTH: SEE TABLE-1(JIS B1115, B1122)
4. FASTENING TORQUE FOR SCREW: 0.392N・m MAX(FOR REFERENCE)
5. AS FOR THE HANDLING OF THIS PRODUCT,
FOLLOW THE INSTRUCTION SHEET No.411-5927.
△. TERTIARY DATUM: [-S-], [-T-] OF EACH BLOCK.
△. MEASURED AT 7.5mm FROM [-Z-].
△. MARKING FOR DESCERMENT OF THE CONTACT FINISH
△. MEASURE AT 2mm FROM [-Z-]
△. ID MARK, PART NUMBER INDICATED.

TABLE-1	プリント基板板厚 (mm)	1.2	1.6
	THICKNESS OF PCB (mm)		
	固定用ねじ着下長さ (mm)	5	6
	NOMINAL LENGTH OF SCREW (mm)		

HOUSING 4±0.4	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	62	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	7~26 29,30,33~50	-	-	NATURAL (自然色)	NATURAL (自然色)	6318750-3	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	9	15.68	Ø2.63	SPS	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	9~14,20~23,25 29,30,37 39~41,44,47	7,8,15~19,24,26 33~36,38,42 43,45,46,48~50	-	BLACK (黒色)	BLACK (黒色)	1-1318750-8	
	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	8	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	-	7~26 29,30,33~50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-6	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	8	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	-	7~26 29,30,33~50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-5	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	5	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	9~14,20~23,25 29,30,37 39~41,44,47	7,8,15~19,24,26 33~36,38,42 43,45,46,48~50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-4	
	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	5	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	9~14,20~23,25 29,30,37 39~41,44,47	7,8,15~19,24,26 33~36,38,42 43,45,46,48~50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-3	
	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	4	15.68	Ø2.63	SPS	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	-	7~26 29,30,33~50	-	BLACK (黒色)	NATURAL (自然色)	1-1318750-2	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	4	15.68	Ø2.63	SPS	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	-	7~26 29,30,33~50	-	BLACK (黒色)	NATURAL (自然色)	1-1318750-1	
	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	6	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	1~6, 27,28,31,32	-	-	7~26,29,30 33~50	-	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-0	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	7	16.72	Ø 2.4	PBT	SELECTIVE-TIN (MATTE)	-	1~6, 27,28,31,32	-	29,48	7~26,30 33~47,49,50	-	NATURAL (自然色)	NATURAL (自然色)	1318750-9	
OBSOLETE	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	3	16.72	Ø 2.4	PBT	SELECTIVE-TIN	-	-	1~6, 27,28,31,32	9~14,20~23,25 29,30,37 39~41,44,47	7,8,15~19,24,26 33~36,38,42 43,45,46,48~50	NATURAL (自然色)	NATURAL (自然色)	1318750-7		
OBSOLETE	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	3	16.72	Ø 2.4	PBT	SELECTIVE-TIN	-	-	1~6, 27,28,31,32	9~14,20~23,25 29,30,37 39~41,44,47	7,8,15~19,24,26 33~36,38,42 43,45,46,48~50	NATURAL (自然色)	NATURAL (自然色)	1318750-6		
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	2	16.72	Ø 2.4	PBT	PRE-TIN TIN LEAD	-	-	1~6, 27,28,31,32	7~26, 29,30,33~50	-	-	NATURAL (自然色)	NATURAL (自然色)	1318750-3	
	CARTON BOX タンボ・ル箱	PLASTIC TUBE プラスチックチューブ	1	16.72	Ø 2.4	PBT	PRE-TIN	-	-	1~6, 27,28,31,32	-	-	7~26, 29,30,33~50	NATURAL (自然色)	NATURAL (自然色)	1318750-2	
	PLASTIC BOX 透明	PLASTIC TUBE プラスチックチューブ	1	16.72	Ø 2.4	PBT	PRE-TIN	-	-	1~6, 27,28,31,32	-	-	7~26, 29,30,33~50	NATURAL (自然色)	NATURAL (自然色)	1318750-1	
	OUTER 外装	INNER 内装						SELECTIVE GOLD	SELECTIVE-TIN (BRIGHT)	PRE-TIN	SELECTIVE GOLD	SELECTIVE-TIN (BRIGHT)	PRE-TIN				
	PACKING STYLE 梱包形態		MARKING (マキング)	WEIGHT (g)	V	HOUSING MATERIAL (ハウジング材料)	SOLDERING SIDE 半田付け側	09011 TAB POWER 				025 TAB SIGNAL 			TINE PLATE COLOR (タインプレート色)	HOUSING COLOR (ハウジング色)	PART NUMBER (型番)
								CONTACT SIDE 接触部側									
								CONTACT FINISH (仕上げ)									



THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN: T. HAYASHI 27APR2000
CHK: N. SAI 27APR2000
APVD: N. SAI 27APR2000

DIMENSIONS:
単位: mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差: ± 0.3
0-PLC: ± 0.1
1-PLC: ± 0.1
2-PLC: ± 0.01
3-PLC: ± 0.001
4-PLC: ± 0.0001
ANGLES: 1/4°-90°

MATERIAL
材料

CONTACT: BRASS
HOUSING: SEE TABLE
TINE PLATE: PBT

FINISH
仕上げ

SEE TABLE

PRODUCT SPEC
製品仕様

108-5667

APPLICATION SPEC
応用仕様

114-5250

WEIGHT
重量

SEE TABLE

CUSTOMER DRAWING


TE Connectivity

025/090 SERIES
50 POSITION CAP ASSEMBLY


SIZE: A1 CASE CODE: 00779 DRAWING NO: ①318750 SHEET 2 OF 2 REV A3

4805 (3/11)

LOC	DIST	REVISIONS 変更				
		P	LTR	DESCRIPTION	ECN	DATE
J	-			SEE 1 OF 2		



CAP ASSEMBLY AND PLUG ASSEMBLY ENGAGEMENT DRAWING
キャップアッセンブリ & プラグアッセンブリ 嵌合図

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. HAYASHI 27APR2000	 TE Connectivity			
		CHK N. SAI 27APR2000				
DIMENSIONS: 単位: ㎜ mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3		NAME 025/090 SERIES 50POSITION CAP ASSEMBLY		
		0-PLC ± 1-PLC ±0.1 2-PLC ±0.01 3-PLC ±0.001 4-PLC ±0.0001 ANGLES ±3'00"				
MATERIAL 材料	SEE 1 OF 2	FINISH 仕上		SIZE A3		
		SEE 1 OF 2		CAGE CODE 00779		
		DRAWING NO 番号 C-1318750				
		RESTRICTED TO —//—				
		SCALE 尺度 2:1				
		SHEET 2 OF 2				
		REV A3				
		CUSTOMER DRAWING				