

Crimping pliers - CRIMPFOX-SC 6-N - 1212689

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 703970
Custom tariff number	82032000
Country of origin	GERMANY

Technical data

General

Length (b)	220 mm
Height	80 mm
Color	black
Die station	Crimping position 1
Min. cross section	0.25 mm ²
Max. cross section	0.5 mm ²
AWG min	24
AWG max	20
Die station	Crimping position 2
Min. cross section	0.5 mm ²
Max. cross section	1 mm ²
AWG min	20
AWG max	18
Die station	Crimping position 3
Min. cross section	4 mm ²
Max. cross section	6 mm ²

Crimping pliers - CRIMPFOX-SC 6-N - 1212689

Technical data

General

AWG min	12
AWG max	10
Die station	Crimping position 4
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Compression	B crimp
Type of contact	Slip-on sleeve

Classifications

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

Accessories

Accessories

Replacement die - CRIMPFOX-WF 6-N/DIE - 1212690



