


# Panels




- Standard, flat 19" rack panels
- Choice of either aluminum (lightweight & easy to machine) or steel (stronger & less expensive)
- Painted versions finished in a tough smooth powder paint finish
- Smooth paint finish for easy labelling
- Unfinished aluminum version is white paper covered on one side to protect finish - also used as a surface for a machining template
- Requires mounting hardware

## ALUMINUM RACK PANELS (0.125" Thick)

| Part Number  |              |                   |              | Panel Height |       | No. of Slots |
|--------------|--------------|-------------------|--------------|--------------|-------|--------------|
| Black Smooth | Beige Smooth | ASA61 Grey Smooth | Unfinished   | Inches       | Units |              |
| PBPA19001BK2 | PBPA19001CG2 | PBPA19001GY2      | PBPA19001UNF | 1.75         | 1     | 4            |
| PBPA19003BK2 | PBPA19003CG2 | PBPA19003GY2      | PBPA19003UNF | 3.50         | 2     | 4            |
| PBPA19005BK2 | PBPA19005CG2 | PBPA19005GY2      | PBPA19005UNF | 5.25         | 3     | 4            |
| PBPA19007BK2 | PBPA19007CG2 | PBPA19007GY2      | PBPA19007UNF | 7.00         | 4     | 4            |
| PBPA19008BK2 | PBPA19008CG2 | PBPA19008GY2      | PBPA19008UNF | 8.75         | 5     | 4            |
| PBPA19010BK2 | PBPA19010CG2 | PBPA19010GY2      | PBPA19010UNF | 10.50        | 6     | 8            |
| PBPA19012BK2 | PBPA19012CG2 | PBPA19012GY2      | PBPA19012UNF | 12.25        | 7     | 8            |
| PBPA19014BK2 | PBPA19014CG2 | PBPA19014GY2      | PBPA19014UNF | 14.00        | 8     | 8            |
| PBPA19015BK2 | PBPA19015CG2 | PBPA19015GY2      | PBPA19015UNF | 15.75        | 9     | 8            |
| PBPA19017BK2 | PBPA19017CG2 | PBPA19017GY2      | PBPA19017UNF | 17.50        | 10    | 8            |
| PBPA19019BK2 | PBPA19019CG2 | PBPA19019GY2      | PBPA19019UNF | 19.25        | 11    | 8            |
| PBPA19021BK2 | PBPA19021CG2 | PBPA19021GY2      | PBPA19021UNF | 21.00        | 12    | 8            |
| PBPA19022BK2 | PBPA19022CG2 | PBPA19022GY2      | PBPA19022UNF | 22.75        | 13    | 8            |
| PBPA19024BK2 | PBPA19024CG2 | PBPA19024GY2      | PBPA19024UNF | 24.50        | 14    | 10           |
| PBPA19026BK2 | PBPA19026CG2 | PBPA19026GY2      | PBPA19026UNF | 26.25        | 15    | 10           |
| PBPA19028BK2 | PBPA19028CG2 | PBPA19028GY2      | PBPA19028UNF | 28.00        | 16    | 12           |
| PBPA19029BK2 | PBPA19029CG2 | PBPA19029GY2      | PBPA19029UNF | 29.75        | 17    | 12           |
| PBPA19031BK2 | PBPA19031CG2 | PBPA19031GY2      | PBPA19031UNF | 31.50        | 18    | 12           |

## STEEL RACK PANELS (14 Gauge, 0.075" Thick)

| Part Number  |              |                   | Panel Height |       | No. of Slots |
|--------------|--------------|-------------------|--------------|-------|--------------|
| Black Smooth | Beige Smooth | ASA61 Grey Smooth | Inches       | Units |              |
| PBPS19001BK2 | PBPS19001CG2 | PBPS19001GY2      | 1.75         | 1     | 4            |
| PBPS19003BK2 | PBPS19003CG2 | PBPS19003GY2      | 3.50         | 2     | 4            |
| PBPS19005BK2 | PBPS19005CG2 | PBPS19005GY2      | 5.25         | 3     | 4            |
| PBPS19007BK2 | PBPS19007CG2 | PBPS19007GY2      | 7.00         | 4     | 4            |
| PBPS19008BK2 | PBPS19008CG2 | PBPS19008GY2      | 8.75         | 5     | 4            |
| PBPS19010BK2 | PBPS19010CG2 | PBPS19010GY2      | 10.50        | 6     | 8            |
| PBPS19012BK2 | PBPS19012CG2 | PBPS19012GY2      | 12.25        | 7     | 8            |
| PBPS19014BK2 | PBPS19014CG2 | PBPS19014GY2      | 14.00        | 8     | 8            |
| PBPS19015BK2 | PBPS19015CG2 | PBPS19015GY2      | 15.75        | 9     | 8            |
| PBPS19017BK2 | PBPS19017CG2 | PBPS19017GY2      | 17.50        | 10    | 8            |
| PBPS19019BK2 | PBPS19019CG2 | PBPS19019GY2      | 19.25        | 11    | 8            |
| PBPS19021BK2 | PBPS19021CG2 | PBPS19021GY2      | 21.00        | 12    | 8            |
| PBPS19022BK2 | PBPS19022CG2 | PBPS19022GY2      | 22.75        | 13    | 8            |
| PBPS19024BK2 | PBPS19024CG2 | PBPS19024GY2      | 24.50        | 14    | 10           |
| PBPS19026BK2 | PBPS19026CG2 | PBPS19026GY2      | 26.25        | 15    | 10           |
| PBPS19028BK2 | PBPS19028CG2 | PBPS19028GY2      | 28.00        | 16    | 12           |
| PBPS19029BK2 | PBPS19029CG2 | PBPS19029GY2      | 29.75        | 17    | 12           |
| PBPS19031BK2 | PBPS19031CG2 | PBPS19031GY2      | 31.50        | 18    | 12           |



## PBPA / PBPS PANELS

### PART No. PBPA & PBPS 19008BK2

PBPA MATERIAL: 0.125" THK ALUMINUM

PBPS MATERIAL: 14 GA. STEEL

