

DYMO®

Facility, Security, and Pro A/V

Rhino™ 4200

All-Purpose Labelling Tool with QWERTY Keyboard



Compact, time-saving labelling for on-the-go pros.

Get labelling jobs done fast – and done right.

The new DYMO® Rhino™ 4200 gets labelling jobs done fast – and done right. Easily navigate the familiar QWERTY keyboard. Use one-touch “Hot Key” shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length labels, breaker labels and more.

Print labels up to 19 mm wide in flexible nylon, permanent polyester and durable vinyl materials – PLUS print directly on heat-shrink tubes. Save even more time with great new features – like the ‘Favorites’ key which provides single-key access to commonly used labels, symbols and terms; and the ‘Custom’ key which eliminates repeated steps by saving customized settings.



DYMO® | Rhino™ 4200 features:

- 1 Easy to navigate computer-style QWERTY keyboard**
Quick and comfortable text entry
- 2 One-Touch “Hot Keys” – a DYMO® exclusive**
Shortcut keys for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length, general and breaker labels
- 3 Industrial-strength labelling versatility**
Print 6 mm, 9 mm, 12 mm and 19 mm wide labels in a variety of materials and colours – PLUS print directly on heat-shrink tubes
- 4 NEW “Favorites” key**
Single-key access to your most commonly used labels, symbols and terms
- 5 NEW “Custom” key prevents needless repetition**
Customize and save settings for individual label formats



Up to

**19
mm**



LABEL APPLICATIONS

LABEL COLOUR

6 mm

9 mm

12 mm

19 mm

24 mm

Labels that stick and stay stuck.

DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces.

LEARN MORE: www.dymo.com/industrial

VINYL

- UL Recognized Component to UL969
- RoHS compliant



Length 5.5 m



WHITE ON BLUE

WHITE ON PURPLE


WHITE ON BROWN

PERMANENT POLYESTER

- UL Recognized Component to UL969
- RoHS compliant



Length 5.5 m



BLACK ON WHITE

BLACK ON CLEAR


BLACK ON METALLIC

HEAT SHRINK TUBES

- UL Recognized Component to UL224
- Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3)
- RoHS compliant



Length 1.5 m



BLACK ON WHITE


BLACK ON YELLOW

FLEXIBLE NYLON

- UL Recognized Component to UL969
- RoHS compliant



Length 3.5 m




BLACK ON WHITE

BLACK ON YELLOW

NON-ADHESIVE TAG

- RoHS compliant

Length 5.5 m



BLACK ON WHITE

SELF-LAMINATING

- RoHS compliant

Length 5.5 m



BLACK ON WHITE

Rhino™ 4200 SINGLE UNIT (BLISTER)

Code: S0955950

Box includes:

- Rhino™ 4200 printer
- Quick reference guide
- 12 mm white vinyl tape

Product specifications:

- Runs on optional rechargeable lithium-ion battery pack or 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 770 gr

Optional accessories:

- AC adapter
- Rechargeable lithium-ion battery pack

Code: S0721430

Code: S0895840

For more information or to find out your nearest distributor, please visit www.dymo.com/industrial or call us at +44 (0) 20 7341 5529.



©2011 DYMO®
DYMO bvba, Industriepark-Noord 30
B9100 Sint-Niklaas, Belgium
www.dymo.com/industrial