



# SPECIFICATIONS

FREQUENCY RANGE: 2 TO 500 MHz  
 NUMBER OF OUTPUT PORTS: 8  
 MINIMUM ISOLATION: 20 dB  
 MAXIMUM VSWR: 1.50  
 MAXIMUM INSERTION LOSS: 2.00 dB



**PASTERNAK ENTERPRISES, INC.**

P.O. BOX 16759, IRVINE, CA 92623  
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
 E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)

**COAXIAL & FIBER OPTICS**

DWG TITLE

**PE2061**

DES.

"75 OHM BNC" FEMALE POWER DIVIDER,  
 FREQUENCY RANGE: 2-500 MHz 8 OUTPUT  
 PORTS

SIZE A

**FSCM NO. 53919**

CAD FILE 032702

SCALE N/A

127

NOTES:

- UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.