

Slim Line

Ultra-low-profile compact keyboard with 86 keys
ML technology with Gold Crosspoint contacts
G84-4100



Keyboard with spill-resistant membrane for laboratory and medical environments.



Other approvals available on request.



Microsoft is a registered trademark of Microsoft Corporation.

General

This high-quality, ultra-flat compact keyboard has been designed for all applications where reduced space requirements and low weight are of great importance.

- For banking/financial applications or medical environments and for portable systems
- Also suitable for 19-inch rack applications
- Ideal for use with Slim Line PCs and notebook computers
- Ideal companion for G84-4700

Key benefits

- Uses mechanical keys from our ML series with high-precision key action; small physical dimensions:
- Keycaps arranged in 18 mm grid
- Exceptionally space-efficient
- Lightweight
- LED indicators for Num Lock, Caps Lock, Scroll Lock
- Reliability:
 MTBF: 170,000 hours
 Individual keys have long service life: 20 million key operations

Technical specifications

- Power supply:
 3.3-5 V/DC $\pm$ 10% SELV
- Current input:
 typ. 10 mA
- Connecting cable:
 approx. 1.70 m long
- Temperature range:
 Storage temperature:
 -20 °C to +60 °C
 Operating temperature:
 0 °C to +50 °C
- Housing dimensions:
 (L x W x H)
 282 x 132 x 27 mm
- Weight:
 approx. 500 g
- ML key modules with
 Gold Crosspoint contacts
- Actuation characteristics:
 Soft contact



External keyboard for pen-based computer.

Order descriptions

- G84-4100 PCM..⁽¹⁾**
 USB interface (Combo, i.e. PS/2 possible using adapter included),
- G84-4100 PTM..⁽¹⁾**
 USB interface (Combo, i.e. PS/2 possible using adapter included), black

⁽¹⁾ International layouts

BE	=	Belgian
CH	=	Swiss
DE	=	German
DK	=	Danish
ES	=	Spanish
FR	=	French
GB	=	English (UK)
IT	=	Italian
NO	=	Norwegian
PO	=	Portuguese
SF	=	Swedish/Finnish
EU	=	English (US) with €

Other versions available on request.