

### Screw Fixing Cable Tie Mounts CTQM


The "2-way" mounting bases CTQM provide a safe guiding of cables and conduits.

- For cable ties up to 5 mm width
- The base is mounted with a screw with countersunk head (max. Ø of head: 8,0mm)

The Q-mount offers a perfect solution in combination with the Q-tie cable ties. It keeps the inserted cable tie in place during pre-assembly and ensures that the Q-tie does not slip out even in difficult situations, for example vertical mounting positions.



Q-mount, CTQM 2-way entry, screwable.



Mounting base CTQM

Material Data	
Material	<b>Polyamide 6.6 (PA66)</b>
Colour	<b>Natural (NA), Black (BK)</b>
Operating Temperature	<b>-40 °C to +85 °C continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



Technical Table								
Article-No.	Type	Length (L)	Width (W)	Height (H)	Fixing Hole Ø (FH)	Strap Width max. (G)	Material	Colour
151-10920	<b>CTQM5</b>	21.0	9.5	6.7	4.5	5.0	PA66	Natural (NA)
151-10930	<b>CTQM5</b>	21.0	9.5	6.7	4.5	5.0	PA66	Black (BK)

All dimensions in mm. Subject to technical changes.