


Model 2383 & 2440 Miniature Insulating Binding Post With Double Mounting Base



FEATURES:

- Accepts miniature banana plugs
- #8-32 hex nut and lockwasher included
- Mounts in panels up to 4.8 (.188) thick

MATERIALS:

Insulated Captive Thumb Nut: Brass

Finish: Model 2383 Gold plated brass

Model 2440 Tin plated brass

Insulation: Polycarbonate. Color: One black and one red

Mounting Base: Black Polycarbonate. Marking: "POMONA ELECTRONICS CALIF.

Insulator: Polycarbonate. One black and one red

Lockwasher: Steel. Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches

Hex Nut: Brass. Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Binding Post: Brass, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel pr MIL-C-26074

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 1500 VDC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 2383-* & 2440-*

*=Color, -0 Black,

Ordering Example: 2383-0 Color is Black

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA