




REF -50 OPTION SCREW  
(WHERE APPLICABLE)




## NOTES:

1. MATERIAL: SEE TABLE
2. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.



4 CIRCUIT SHOWN



| ITEM |    | QTY                                              | DESCRIPTION   | MATERIAL           | FINISH |
|------|----|--------------------------------------------------|---------------|--------------------|--------|
| 6    | XX | SCREW&WASHER, 6-32X.250, PAN, PH/SL (-50 OPTION) | STEEL         | ZN, CLEAR CHROMATE |        |
| 5    | XX | SCREW, 6-32X.250, BHD, PHIL-SLOT (-49 OPTION)    | BRASS         | NICKEL             |        |
| 4    | XX | SCREW, 6-32X.250, BHD, PHIL-SLOT (STANDARD)      | STEEL         | ZN, CLEAR CHROMATE |        |
| 3    | XX | TERMINAL, SOLDER TURRET                          | BRASS         | TIN                |        |
| 2    | XX | MOUNTING PLATE                                   | BRASS         | NICKEL             |        |
| 1    | 1  | INSULATOR, SR, W/MTG                             | THERMOPLASTIC | BLACK              |        |

|                    |  |                 |  |                                       |  |                 |  |                                                                                                                               |  |                        |  |                        |  |
|--------------------|--|-----------------|--|---------------------------------------|--|-----------------|--|-------------------------------------------------------------------------------------------------------------------------------|--|------------------------|--|------------------------|--|
| INITIAL RELEASE    |  | QUALITY SYMBOLS |  | GENERAL TOLERANCES (UNLESS SPECIFIED) |  | DIMENSION STYLE |  | SCALE                                                                                                                         |  | DESIGN UNITS           |  | THIRD ANGLE PROJECTION |  |
| EC NO: ET2007-0073 |  | 2006/09/28      |  | mm                                    |  | MM/IN           |  | 2:1                                                                                                                           |  | INCH                   |  |                        |  |
| DRWN:EHILE         |  | 2006/09/28      |  | INCH                                  |  | DATE            |  | TITLE                                                                                                                         |  |                        |  |                        |  |
| CHKD:JMACNEIL      |  | 2006/09/28      |  | 4 PLACES ± ---                        |  | EHILE           |  | 2006/09/13                                                                                                                    |  | 9.53MM [.375] SR BTS   |  |                        |  |
| APPR:JMACNEIL      |  | 2006/09/29      |  | 3 PLACES ± ---                        |  | CHECKED BY      |  | DATE                                                                                                                          |  | ASSY, INSULATED TURRET |  |                        |  |
|                    |  |                 |  | 2 PLACES ± 0.13                       |  | JMACNEIL        |  | 2006/09/13                                                                                                                    |  | TERMINAL W/MTG         |  |                        |  |
|                    |  |                 |  | 1 PLACE ± 0.25                        |  | APPROVED BY     |  | DATE                                                                                                                          |  | MOLEX INCORPORATED     |  |                        |  |
|                    |  |                 |  | ANGULAR ± 2 °                         |  | JMACNEIL        |  | 2006/09/13                                                                                                                    |  | MOLEX                  |  |                        |  |
|                    |  |                 |  | DRAFT WHERE APPLICABLE                |  | MATERIAL NO.    |  | DOCUMENT NO.                                                                                                                  |  | SHEET NO.              |  |                        |  |
|                    |  |                 |  | MUST REMAIN                           |  | SEE CHART       |  | SD-38720-010                                                                                                                  |  | 1 OF 2                 |  |                        |  |
|                    |  |                 |  | WITHIN DIMENSIONS                     |  | SIZE            |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  |                        |  |                        |  |
| A                  |  | REV             |  |                                       |  | B               |  |                                                                                                                               |  |                        |  |                        |  |

