



CAT 5E RJ45 Ethernet Patch Cable

CAT5E Patch Cable for Connecting Your Ethernet Peripherals to your Network

PC5-CC-XX*

Without a way to connect computers to one another you cannot have a network. As a result your network is only as good as your infrastructure. Improve your network's connectivity with Cat5e patch cables. The connectors ensures the best level of conductivity between the cable and your network peripherals. Designed according to the TIA/EIA 568 B-2 specification. This cable is used to connect a computer to a wall, patch panel to a hub, switch or like device.



Featured Product Benefits

- Premium Quality
- Supports 10 Mbps, 100 Mbps & Gigabit Ethernet
- Gold Contacts
- Multiple colors available for easy identification
- Molded boot to keep proper radius when connected to a patch panel and/or a computer.
- Snagless cover for retaining clip.

***CC= Color**

***XX=Length**



CAT 5e

† Key for Colors

BK=Black, BL=Blue, GR=Green, GY=Gray, OR=Orange, PL=Purple, RE=Red, WH=White, YL=Yellow

Item Number		Length
PC5-_-02	_ = BK, BL, GR, GY, OR, RE, WH, YL †	2 Feet
PC5-_-03	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	3 Feet
PC5-_-04	_ = BK, BL, GY, YL †	4 Feet
PC5-_-05	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	5 Feet
PC5-_-06	_ = BL, GY, YL †	6 Feet
PC5-_-07	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	7 Feet
PC5-_-08	_ = BL †	8 Feet
PC5-_-10	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	10 Feet
PC5-_-14	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	14 Feet
PC5-_-15	_ = BK, BL, GY, YL †	15 Feet
PC5-_-20	_ = BK, BL, GY, YL †	20 Feet
PC5-_-25	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	25 Feet
PC5-_-35		35 Feet
PC5-_-50	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	50 Feet
PC5-_-75	_ = BL, WH †	75 Feet
PC5-_-100	_ = BK, BL, GY, RE, WH, YL †	100 Feet
PC5-_-01	_ = BK, BL, GR, GY, OR, PL, RE, WH, YL †	1 Foot

© Copyright 2007 Jo-Dan International, Inc. all rights reserved. Plus Series®, PowerCore®, QuickConnect®, Share Plus®, and GoldX® Products are registered trademarks of Jo-Dan International, Inc. All other trademarks and registered trademarks are the property of their respective owners. Designed in USA. Made in China. One or more of the following patents may apply: D494,935, D494,934, D494,932, D493,453, 6,755,676, D490,702, 6,736,658, 6,726,509, 6,716,047, D485,752, D484,044, D481,629, D481,628, 6,607,408, D478,001, D478,000, D468,635, 6,479,607, D465,223, 6,454,584, D462,612, D452,427, D452,426, D451,888, D451,480, D450,303, D448,736, D444,772, D443,862, D443,593, D442,919, D442,556, D442,555, 5,788,521, 5,658,158, 5,334,033, 5,292,257. D503,882; 6,843,684; 6,854,989; 6,872,086; D506,386; 6,905,374; D509,797; 6,991,483; D513,976; 7,004,787; 7,028,114; D519,925; D522,507; 7,258,572. Other patents pending.

(800) 596-5100

www.jditech.com