

**RS Part Ref : 500-0881**


**RS Part Ref : 500-0897**

The Aphel DB3000M is the socket strip of choice for 19" technology racking systems, enclosures and associated applications. This product is bus bar wired at a rating of 32A.

**DB3000M UK 32A**

The Socket Strip of Choice

**Power Connectivity**



## Dimensional Data

| Part Reference | Length | Width | Depth |
|----------------|--------|-------|-------|
| 500-0881       | 548mm  | 56mm  | 49mm  |
| 500-0897       | 1020mm | 56mm  | 49mm  |


## Features

- Robust aluminium enclosure
- Engineering polycarbonate moulded parts
- Multiple mounting methods
- External earth take off point (6.3mm tab. For safety earth bonding of external surfaces.

## Specifications

- Input Type: EN60309 (BS4343) 32A
- Outlet Type: UK 13A 8W
- Cable Type: 4 SQMM HO7 RNF
- Ratings: 32A, 250V~

## Extrusion Profile



**Mounting Features** – See leaflet 38 for fixing instructions

Please call 0870 754 1880 or email: [sales@aphel.co.uk](mailto:sales@aphel.co.uk) to discuss your requirements.