

# T&B® Fittings



## Non-Metallic Sheathed Cable Conduit Fittings T&B Catalog Number:

3302M-TB

78621080552

Active

### Description:

1/2 in. Insulated Two Screw Connector, Steel-Electro Zinc Plated.

### Features

Rounded cable grip and smooth bushing protect the cable sheath and wire insulation. Since saddle is threaded, screws do not travel or extend beyond the connector body as it is clamped to the cable. An extra lip on the saddle closes the unused part of the connector opening.

### Application

To connect non-metallic sheathed cable and flexible cord to a box or an enclosure.

### General

Material	Steel
Finish	Electro Zinc Plated

### Dimension Information

Dimension A (inches)	31/32
Dimension B (inches)	1 3/8
Dimension C (inches)	1 3/16
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.250
Cable Opening-Maximum (inches)	0.590

### Specifications

3dmodel	Available on Website
---------	----------------------

### Packaging

T&B Inner Pack	100
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	6.54 lbs. per 100

### Notes

\*Note U.L. listed and CSA certified for the following single (1) and pairs of (2) NM and NMC cable; (1) 2#14, 2#12, 2#10, 3#14, 3#12, 3#10, (2) 2#14, 2#12.

\*\*Note U.L. listed and CSA certified for the following Service Entrance Cables; 2#12 thru 2#4, 3#12, 3#10.

### Certifications

RoHS Compliance	Yes
-----------------	-----

**Certifications**

File Nbr:  
E 17583

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)