

# TERMINAL BLOCKS & BARRIER STRIPS

## 30 Amp Dual Row Terminal Blocks

### Specifications:

**Rating:** 30A, 300V

**Center Spacing:** .375" or 3/8" (9.52 mm)

**Wire Range:** #14-22 AWG CU

**Screw Size:** #6-32 phillslot screws

**Torque Rating:** 9 in-lb

**Distance Between Barriers:** .30" (7.62 mm)

**Mounting:** #6 screws

**Operating Temperature:** 130°C (266°F) Max.


-40°C (-40°F) Min.

**Materials:** Molded base: Black, UL rated 94VO thermoplastic

Terminal plating: Tin over brass; Screws: Zinc plated steel

**Breakdown Voltage:** 3600V

**Agency Information:** UL/CSA; IEC Compliance; CE Certified



| Part Number | No. Poles | "A" dim. | "B" dim. |
|-------------|-----------|----------|----------|
| 13-1402     | 2         | 1.40"    | 1.12"    |
| 13-1403     | 3         | 1.78"    | 1.50"    |
| 13-1404     | 4         | 2.16"    | 1.88"    |
| 13-1405     | 5         | 2.53"    | 2.25"    |
| 13-1406     | 6         | 2.90"    | 2.62"    |
| 13-1407     | 7         | 3.28"    | 3.00"    |
| 13-1408     | 8         | 3.66"    | 3.38"    |
| 13-1409     | 9         | 4.03"    | 3.75"    |

| Part Number | No. Poles | "A" dim. | "B" dim. |
|-------------|-----------|----------|----------|
| 13-1410     | 10        | 4.40"    | 4.12"    |
| 13-1412     | 12        | 5.16"    | 4.88"    |
| 13-1414     | 14        | 5.90"    | 5.62"    |
| 13-1416     | 16        | 6.66"    | 6.38"    |
| 13-1418     | 18        | 7.40"    | 7.12"    |
| 13-1420     | 20        | 8.16"    | 7.88"    |
| 13-1422     | 22        | 8.90"    | 8.62"    |

## Heavy Duty 30 Amp Dual Row Terminal Blocks

### Specifications:

**Rating:** 30A, 300V

**Center Spacing:** .437" or 7/16" (9.52 mm)

**Wire Range:** #12-22 AWG CU

**Screw Size:** #6-32 phillslot screws

**Torque Rating:** 9 in-lb

**Distance Between Barriers:** .353" (8.97 mm)

**Mounting:** #6 screws

**Operating Temperature:** 130°C (266°F) Max.



-40°C (-40°F) Min.

**Materials:** Molded base: Black, UL rated 94VO thermoplastic

Terminal plating: Tin over brass; Screws: Zinc plated steel

**Breakdown Voltage:** 4800V

**Agency Information:** UL/CSA; IEC Compliance; CE Certified



| Part Number | No. Poles | "A" dim. | "B" dim. |
|-------------|-----------|----------|----------|
| 13-1502     | 2         | 1.63"    | 1.31"    |
| 13-1503     | 3         | 2.07"    | 1.75"    |
| 13-1504     | 4         | 2.51"    | 2.18"    |
| 13-1505     | 5         | 2.94"    | 2.62"    |
| 13-1506     | 6         | 3.38"    | 3.06"    |
| 13-1507     | 7         | 3.82"    | 3.50"    |
| 13-1508     | 8         | 4.25"    | 3.93"    |
| 13-1509     | 9         | 4.69"    | 4.37"    |

| Part Number | No. Poles | "A" dim. | "B" dim. |
|-------------|-----------|----------|----------|
| 13-1510     | 10        | 5.13"    | 4.81"    |
| 13-1512     | 12        | 6.00"    | 5.68"    |
| 13-1514     | 14        | 6.87"    | 6.56"    |
| 13-1516     | 16        | 7.75"    | 7.43"    |
| 13-1518     | 18        | 8.62"    | 8.31"    |
| 13-1520     | 20        | 9.50"    | 9.18"    |
| 13-1522     | 22        | 10.37"   | 10.06"   |