



PC112-H25D-T120

Pan-Clamp™ Heavy Duty Fixed Diameter Clamp

Std. Pallet Weight (lb)	0.0000
Std. Pkg. Qty.	200
Std. Ctn. Volume (cf)	2.6641
Std. Ctn. Weight (lb)	15.3000
Std. Pallet Volume (cf)	0.000000
RoHS Compliancy Status	Compliant
Part Description	Pan-Clamp™ Heavy Duty Fixed Diameter Clamp
Product Type	Wire Clips - Push Mount
Material	Weather Resistant Nylon 12
Color	Black
Width (mm)	15.7
Width (In.)	0.62
Panel Thickness (mm)	3.2
Panel Thickness (In.)	0.125
Panel Hole Diameter (mm)	7.1
Panel Hole Diameter (In.)	0.28
Max. Panel Thickness (mm)	3.2
Max. Panel Thickness (In.)	0.13
Max. Bundle Diameter (mm)	28.5
Max. Bundle Diameter (In.)	1.13
Environment	Outdoor
Mounting Method	Push Barb
Pricing Description	Pan-Clamp 1.12 Inches (28.5mm) Bundle with Integrated Fastener, Weather Resistant Nylon 12
Type	Wire Clips - Push Mount
CE Compliant	No
Bundle Offset (In.)	1.02
Bundle Offset (mm)	25.8
Min. Order Qty.	200.0000