

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130106-0112](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway™ Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets, Overall Length 7.62m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Literature Order No	987650-8055
Product Name	Super-Safeway™
Type	String Lights
UPC	78678879893
Woodhead	Yes

Physical

Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	107.95mm (4.250")
Length	15.24m (50.0')
Material - Guard	N/A
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded

Electrical

Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number	323523
-----------------	--------



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130106Series](#)