



PART NAME	SERIES 30-2000 UPRIGHT ADD-A-RACK	PART No.	A30-2032	TD	A30-2039	REV.	1-2-02
-----------	-----------------------------------	----------	----------	----	----------	------	--------

FINISH:
 FRAME ASSEMBLY, _____
 DOOR & TOP COVER _____
 ROYAL BLUE TEXTURE
 PANEL MOUNTING RAILS _____
 SMOOTH BLACK
 FRONT TOP TRIM _____
 METALLIC GRAY


MATERIAL:
 PANEL MOUNTING RAILS _____ 12 GA. STEEL
 FRAME TOP, BASE ASSEMBLY, _____
 FILLERS & VERTICAL RAILS _____ 14 GA. STEEL
 RAIL SUPPORTS _____ 16 GA. STEEL
 TOP COVER _____ 18 GA. STEEL
 DOOR & FRONT TOP TRIM _____ 20 GA. STEEL



PANEL MOUNTING RAILS (FRONT & REAR)
 ARE TAPPED #10-32 ON C.I.A. UNIVERSAL
 SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR MOUNTING RC-7758 CASTERS.

LOAD RATING: 1200 LBS. MAX.



* DISCONTINUED

PART No.	P.S.	A	B	C	D	E	F	G	H	J
A30-2032	21.000	30.250	29.000	27.500	18.937	—	—	—	—	—
* A30-2033	31.500	40.750	39.500	38.000	29.437	—	—	—	—	—
* A30-2034	35.000	44.250	43.000	41.500	32.937	—	—	—	—	—
A30-2035	42.000	51.250	50.000	48.500	—	19.281	17.906	—	—	—
A30-2036	52.500	61.750	60.500	59.000	—	24.531	23.156	—	—	—
A30-2037	61.250	70.500	69.250	67.750	—	28.906	27.531	—	—	—
A30-2038	70.000	79.250	78.000	76.500	—	33.281	31.906	—	—	—
A30-2039	78.750	88.000	86.750	85.250	—	—	—	25.125	22.312	23.750

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bud Industries:

[A30-2032-GT](#) [A30-2032-RB](#) [A30-2035-GT](#) [A30-2035-RB](#) [A30-2036-GT](#) [A30-2036-RB](#) [A30-2037-GT](#) [A30-2037-RB](#)
[A30-2038-GT](#) [A30-2038-RB](#) [A30-2039-GT](#) [A30-2039-RB](#)