

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2003 By —

LOC

J

	DIST
--	------

—

REVISIONS

变更

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


H2

REVISÉ PER ECO-11-005140

28MAR11

RK

HMR




注；

- 1 使用ハウジング型番 172021,172047 他
- 2 製品規格: 108-5124
- ③ 全面ニッケルめっきの上に4.5mmの部分に0.38 μ m以上の金めっき
- ④ 全面ニッケルめっきの上に接触バネ内側 1.6mmの部分に0.38 μ m以上の金めっき
コンタクト先端 0.9mmのところに金フラッシュめっき
- ⑤ 1-170291-1の逆巻きリール

NOTES;

- 1 MATABLE HOUSING: 172021, 172047 AND OTHERS
2 PRODUCT SPECIFICATION: 108-5124
3 0.38μm MIN. SELECTIVE GOLD PLATING IN 4.5mm LENGTH OVER
NICKEL PLATING
4 0.38μm MIN. SELECTIVE GOLD IN 1.6mm LENGTH (INSIDE OF LEAF) OVER
NICKEL PLATING, GOLD FLASH PLATING IN TIP OF CONTACT 0.9mm LENGTH
5 REVERSE REEL OF 1-170291-1

		型番 (NUMBER)	材料 (MATERIAL)	仕上 (FINISH)	バラ端子型番 (L/P PART NUMBER)
OBSOLETE		1-170291-1	黄銅, BRASS, 0.3t	錫めっき済 PRE-TINND MAT'L	1-170321-1
		1-170291-3	黄銅, BRASS, 0.3t		—/—
		1-170291-4	リン青銅, 0.3t PHOS-BZ	錫めっき済 PRE-TINND MAT'L	1-170321-4
		1-170291-7	リン青銅, 0.3t PHOS-BZ		—/—
		3-170291-1	黄銅, BRASS, 0.3t	錫めっき済 PRE-TINND MAT'L	—/—

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.YAMAGUCHI		09JUL03		TE Connectivity						
		CHK K.BETSUI		09JUL03								
DIMENSIONS: 単位：耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3		APVD K.BETSUI		09JUL03		NAME 名称 DUAL LINE INTERLOCK CONNECTOR				
		±1°		PRODUCT SPEC 製品規格 108-5124								
		±1°		APPLICATION SPEC 取付適用規格 114-5045								
WIRE RANGE 0.3~0.56mm ² (AWG#22-#20)		MATERIAL 材料		FINISH 仕上		WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-170291	RESTRICTED TO —	
INSULATION DIA. 2.4mm MAX.		SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 尺度 5:1	SHEET 1 OF 1	REV H2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-170291-1 \(Mouser Reel\)](#) [1-170291-1 \(Cut Strip\)](#)