



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.	ALL RIGHTS RESERVED.

CONNECTOR ASSEMBLY EXEMPLARY LOADED




CONTACT DIMENSIONS




RECOMMENDED PCB-HOLE LAY-OUT

COMPONENT SIDE SHOWN



CONTACT LAYOUT



NOTES:

- 1 MATERIAL HOUSING : GREY GLASSFILLED POLYESTER
UL-RATING V0
CONTACT : PHOSPHORBRONZE
- 2 GENERAL CONTACT PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
REDUCED CROSS-TALK SHIELD: GOLD FLASH OVER 1,27µm NICKEL MIN.
- 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4 CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.
- 5 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
- 6 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
- 7 PLATED SPOT ONLY ON COMPONENT SIDE, FORMING ONE CONTACT
WITH PLATED THROUGH HOLES OF ROW C

P.C.B. HOLE DIM. ACTION PIN
FIN. HOLE : 0,55 TO 0,65mm
OTHER REQUIREMENTS SEE
APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L.V.D.HEIJDEN	12FEB98	tyco Electronics		Tyco Electronics Corporation s - HertogenBosch, Netherlands,					
DIMENSIONS: mm			CHK D.TRUREN	12FEB98								
			APVD F.V.KONINGSBRUGGE	—	NAME Z-PACK 2MM HM TYPE C							
			PRODUCT SPEC 108-19082		55 POS. RIGHT ANGLE MALE CONNECTOR WITH REDUCED CROSS-TALK SHIELDS							
			APPLICATION SPEC 114-19029		SIZE A2		CAGE CODE 00779	DRAWING NO C-352273		RESTRICTED TO —		
			WEIGHT —									
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH			CUSTOMER DRAWING									
MATERIAL —					SCALE NTS		SHEET 1 OF 1		REV F			