

Product Description

Fast assembly; Easy to disassemble; Tear-proof connection; No slack in the conduit; No loose parts



Application range

- In combination with protective conduit
- SILVYN® RILL PA6
- SILVYN® RILL PA12
- Fastening of conduits on machine walls for all applications

Benefits

- Fast assembly
- Easy to disassemble
- Tear-proof connection
- No slack in the conduit
- No loose parts

Design

- One-piece conduit holder with M4/M5/M6 borehole for fixation

Approvals

- UL FILENUMBER E308201

Product features

- Impact-resistant polyamide
- One-piece conduit holder

- Suitable for mounting onto a C-profile rail
- Stackable

Technical Data

Colour delivered

Grey (RAL 7001) Black (RAL 9005), UV-resistant

Temperature range

-40 °C to +115 °C

Material

PA6

Article List

Part number	PG size	Pieces / PU
SILVYN® KLICK-RH grey		
65500300	7	50
65500310	9	50
65500320	11	50
65500330	13.5	50
65500340	16	50
65500350	21	25
65500360	29	25
65500370	36	25
65500380	48	10
SILVYN® KLICK-RH black		
65500305	7	50
65500315	9	50
65500325	11	50
65500335	13.5	50
65500345	16	50
65500355	21	25
65500365	29	25
65500375	36	25
65500385	48	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.