


REV.	DATE	ECR NO.	DESCRIPTION
A	05/21/02	—	MODIFY PART DESCRIPTION
B	09/29/08	—	REVISE BODY DESIGN



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	GRS						09/29/08
7						CHECKED			PART DESCRIPTION 7/16 FEMALE TO 7/16 MALE R/A ADAPTER				
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	ISSUED							
5						SHEET	1 OF 1						
4									PART NO. 272150				
3	CONTACT PIN	BER. COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	CAD FILE C:/272/272150.DWG		DWG. NO.					
2	INSULATOR	PTFE	NATURAL	1									
1	BODY	BRASS	NEXCOTE	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING								