




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. | FLANGE<br>THICKNESS           | WEIGHT<br>lbs 10<br>(g) pcs |
|---------------------|-------------------------------|-----------------------------|
| JP131SBC87R- ---    | UP TO 3/4"<br>(19.05mm) THICK | 3.9<br>(1769.01)            |

#### NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- |                         |                      |
|-------------------------|----------------------|
| HOOK MATERIAL:          | NYLON 6/6            |
| ANGLE BRACKET MATERIAL: | PRE-GALVANIZED STEEL |
| CLAMP MATERIAL:         | MALLEABLE IRON       |
| RIVET MATERIAL:         | ALUMINUM             |
| LOCK WASHER:            | ZINC PLATED STEEL    |
| BOLT:                   | ZINC PLATED STEEL    |
- PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 1 5/16" (33.34) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 25 lbs.
- PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- PRODUCT MARKINGS:  
  - cULus logo and statement:  
 "SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
  - ULC logo and statement:  
 "IN ACCORDANCE WITH CAN/ULC S-102.2 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=20."

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

10K016DK\_DC\_GB3043CP/01A

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

J-PRO J-HOOK WITH 360°  
ROTATION SCREW ON BEAM CLAMP  
(JP131SBC87R- ---)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ±0.05 (1.31 (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.

|     |          |     |     |                                                                            |          |     |      |     |    |
|-----|----------|-----|-----|----------------------------------------------------------------------------|----------|-----|------|-----|----|
| OIA | 09/08/10 | JAD | DJW | UPDATED BEAM CLAMP TO NEW VERSION,<br>UPDATED DRAWING TO TEAMCENTER FORMAT | GB3034CP | OIA | KLN  |     |    |
| I   | 2/20/06  | JAD |     | FLANGE THICKNESS WAS 7/8"                                                  | GB3034CP | I   |      |     |    |
| REV | DATE     | BY  | CHK | DESCRIPTION                                                                | ECN      | - R | CUST | SUP | OC |

DRAWN BY

JAD

MAT'L:

SEE NOTE 2

DATE

1/19/06

CHK'D

KLN

SCALE

NONE

DRAWING NO.

GB3043CP

DWG

A  
SIZE