


DC Jack 6.5 x 3.5 x 1.4




163-1203-E

KOBI CONN

DC Jack 6.5 x 3.5 x 1.4



SCHEMATIC



RECOMMENDED P.C.B LAYOUT (COMPONENT SIDE)
P.C.B THICKNESS = 1.6MM

Dimensions: mm

ELECTRICAL SPECIFICATIONS

Current Rating:	250 VAC Max.
Voltage Rating:	24V AC/DC Max.
Contact Resistance:	30mΩ Max.
Insulation Resistance:	100MΩ Min.
Dielectric Voltage:	500V AC/Min.
RoHS Compliant	

MATERIAL SPECIFICATIONS

Housing:	High Temp. Plastic, Black
Terminal:	Copper Alloy
Terminal Plating:	Silver on contact and solder all over nickel
RoHS Compliant	

Date Last Revised: 6-13-12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301345

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-1203-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-1203-E](#)