

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0210200436](#)
Status: **Active - Custom**
Overview:
Description: 0.50mm (.020") Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 40 Circuits, 0.152m (6.00") Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Cable
Series [21020](#)
Comments Contacts on opposite sides, Type D
Geographic Area Americas
Overview Premo-Flex™
Product Name Premo-Flex™ FFC Jumper

Physical
Cable Length 0.152m (6.00")
Circuits (Loaded) 40
Packaging Type Bag
Pitch - Term. Interface (in) 0.020 In
Pitch - Term. Interface (mm) 0.50 mm
Temperature Range - Operating -40°C to +80°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum 0.5A
Voltage - Maximum 30V

Solder Process Data
Duration at Max. Process Temperature (seconds) 30
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 250

Material Info



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[21020 Series](#)

Use With
Any 0.50mm (.020") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION