

F

E

D

C

B

A

10

9

8

7

6




5

4

3

2

1



MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140055	BTY601P-FBB	-

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 A PER PORT, 12 AMPS MAX.
PROTECTION	IP67
OPERATING TEMPERATURE	-25°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR

DESCRIPTION EC NO: WEU2010-0451 DRWN: LSTEMMLE 2010/03/22 CHKD: NS APPR: FPACHER 2010/03/23	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY DATE LSTEMMLE 2010/03/22		MICRO-CHANGE MPIS 6 PORT PNP TWIN PORT 5P 12 P HARD SHELL CONN.			
		4 PLACES	±---	±---	CHECKED BY DATE FP 2010/03/23					
		3 PLACES	±---	±---	APPROVED BY DATE FPACHER 2010/03/23					
		2 PLACES	±---	±.01	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-120114-077		SHEET NO. 1 OF 1	
		1 PLACE ±0.3 ±---			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
		ANGULAR ± --- °								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
1	REV									

10

9

8

7

6

5

4

3

2

1