







Jack


161-3505

KOBI CONN

Jack



Schematic



Panel Cut-out

Dimensions: In.
(except where noted)

SPECIFICATIONS	
Type:	PCB mount, 3.5mm, mono, phone jack
Contact resistance:	30mΩ max.
Insulation resistance:	100MΩ min. @ 500VDC
Withstand voltage:	500VAC for 1 minute
Terminals:	silver plated brass
Metal tip:	nickel plated brass
Housing:	Noryl, UL 94V-1
Housing color:	black

Date Last Revised: 4-5-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300421

161-3505

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3505](#)